

Product sheet



LEGRAND

RCBO - DX³ 6000 -10 kA -1P+N-230 V~ -25 A -30 mA - A type -N right hand

REF. 411052 | EAN. 3245064110525

[> Visit e-catalogue](#)

Product characteristics

- RCBOs DX³ 6000 - 10 kA - residual current circuit breakers from 3 A to 63 A - AC, A and F types - Conform to IEC 61009 - 1, IEC 62423 (F type) - Compatible with prong - type and fork type supply busbars - Voltage independent tripping - Breaking capacity : - 6000 - IEC 61009 - 1 - 10 kA / IEC 60947 - 2 for single pole + neutral, 2 and 4-pole - AC type : detect AC component faults - A type : detect AC and DC component faults - F type (High immunity) : detect AC and pulsating DC residual currents - Enhanced immunity to unwanted tripping in disturbed environments - Detection of high frequency fault currents - Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls
- Single pole + neutral - 230 V~ - Neutral on Right - hand side A Type 30 mA - C curve - Nominal rating In : 25 A - Number of modules : 2

Documentation

TECHNICAL DOCUMENTATION

F01573EN-05.pdf | PDF (1.08Mo)

CAD & Design specs / BIM

411002.dwg | DWG (0.18Mo)

CATALOGUE PAGE & OTHERS

ex223001_0076-0077.pdf | PDF (0.2Mo)

ex223001_0062.pdf | PDF (0.08Mo)

Agreements & Certificates

OC / CB-CB FR_700911/M1 | (0.94Mo)

LGRP-00748-V02.01-FR.pdf | PDF (0.65Mo)

NF-NF012_4076 | (0.55Mo)

LGRP-00748-V02.01-EN.pdf | PDF (0.6Mo)