

# Product sheet



LCS<sup>3</sup> LEGRAND

Patch panel 19 inch - empty cassettes to be equipped with 24 RJ45

REF. 033790 | EAN. 3414970870780

This 19 inch patch panel has a new generation quick-fix mechanism for automatic screwless mounting on the cabinets uprights. The automatic removal of each cassette is possible using a push button.

> [Visit e-catalogue](#)

## Description

This 19 inch patch panel has a new generation quick-fix mechanism for automatic screwless mounting on the cabinets uprights. The automatic removal of each cassette is possible using a push button.

### Product characteristics

- Equipped with 4 extractable cassettes.
- Equipped with rear cable guide to hold the cables.
- 19" panel - 1 U.
- Supplied with coloured labels, white yellow, blue and red.

### Recommendation / Restriction

- Compliant with ISO/IEC 11801 edition 3.0 (2017) and EIA/TIA 568 C2-1 standards

## The product's benefits

### Installation

- Front-panel and fast-snap accessibility of each individual connector provide ease and reliability for installation and maintenance. Universal and secured mounting on any cabinet or enclosure through new generation quick-fix anchorage. Automatic cassette removal by a simple button press. Hands-free cassette support during installation or maintenance while in the extracted position.

### Usage

- Daily user maintenance is rendered easy through the move-add-change management of each cassette and individual connector.

### Avantages

- Save time at both installation and in daily maintenance by taking advantage of the screwless mounting and the automatic removal of each cassette.

## Documentation

### TECHNICAL DOCUMENTATION

- [LE09727AD.pdf](#) | PDF (4.73Mo)
- [S000099427FR-01.pdf](#) | PDF (1.81Mo)
- [S000099427EN-00.pdf](#) | PDF (1.74Mo)

### CATALOGUE PAGE & OTHERS

- [ex223001\\_0976.pdf](#) | PDF (0.15Mo)
- [ex223001\\_0978.pdf](#) | PDF (0.16Mo)
- [ex223001\\_0989.pdf](#) | PDF (0.16Mo)
- [ex223001\\_0983.pdf](#) | PDF (0.16Mo)

## Agreements & Certificates



LGRP-00867-V01.01-EN.pdf | PDF (0.58Mo)