

Product sheet



LCS³ LEGRAND

Patch panel 19 inch - to be equipped with cassettes and 24 RJ45

REF. 033791 | EAN. 3414970870803

This 19 inch patch panel has a new generation quick-fix mechanism for automatic screwless mounting on the cabinets uprights. The automatic removal of each cassette is possible using a push button.

> [Visit e-catalogue](#)

Description

This 19 inch patch panel has a new generation quick-fix mechanism for automatic screwless mounting on the cabinets uprights. The automatic removal of each cassette is possible using a push button.

Product characteristics

- Equipped with rear cable guide to hold the cables.
- 19" panel - 1 U.
- Supplied with coloured labels, white yellow, blue and red.

Recommendation / Restriction

- Compliant with ISO/IEC 11801 edition 3.0 (2017) and EIA/TIA 568 C2-1 standards

The product's benefits

Installation

- Front-panel and fast-snap accessibility of each individual connector provide ease and reliability for installation and maintenance. Universal and secured mounting on any cabinet or enclosure through new generation quick-fix anchorage. Automatic cassette removal by a simple button press. Hands-free cassette support during installation or maintenance while in the extracted position.

Usage

- Daily user maintenance is rendered easy through the move-add-change management of each cassette and individual connector.

Avantages

- Save time at both installation and in daily maintenance by taking advantage of the screwless mounting and the automatic removal of each cassette.

Documentation

TECHNICAL DOCUMENTATION

- [LE09727AD.pdf](#) | PDF (4.73Mo)
- [S000104244EN-04.pdf](#) | PDF (0.12Mo)
- [S000099438FR-04.pdf](#) | PDF (1.91Mo)
- [S000099438EN-04.pdf](#) | PDF (1.91Mo)

CATALOGUE PAGE & OTHERS

- [ex223001_0976.pdf](#) | PDF (0.15Mo)
- [ex223001_0978.pdf](#) | PDF (0.16Mo)
- [ex223001_0994.pdf](#) | PDF (0.12Mo)
- [ex223001_0989.pdf](#) | PDF (0.16Mo)

 [ex223001_0983.pdf](#) | PDF (0.16Mo)

Agreements & Certificates

 [LGRP-00626-V02.01-FR.pdf](#) | PDF (0.96Mo) [LGRP-00626-V02.01-EN.pdf](#) | PDF (0.95Mo)