

Product sheet



LCS³ LEGRAND

Optic drawer 19 inches 1U rotating equipped with 36 LC duplex multi-mode connectors for 72 fibres

REF. 032171 | EAN. 3414970958426

[> Visit e-catalogue](#)

Product characteristics

- Maximum capacity : 36 LC multimode connectors for 72 fibres
- Rotating : supplied with Left - to - Right opening, reversible.
- Panel and optic port marking on dedicated marking areas
- Height 1U, depth 220mm
- Black color

Recommendation / Restriction

- Up to 72 fibers. Suitable for a large number of active devices. Recommended in the generic standards ISO/IEC 11801 and EN 50173.

The product's benefits

Installation

- Supplied with screws and wiring accessories : 4 screws and nuts/4 screws, 2 cable glands (1 x PG16/1 x PG13.5), 2 accessories for coiling the fibres, 1 drawer holder for fixing on the rack, 1 splice holder, fitted but repositionable

Usage

- Panel and optical ports marked on dedicated marking area.

Avantages

- Panel marking area for labelling

Documentation

TECHNICAL DOCUMENTATION

- [S000095448FR-00.pdf](#) | PDF (1.48Mo)
- [S000095448EN-00.pdf](#) | PDF (1.08Mo)
- [LE09649AB.pdf](#) | PDF (3.4Mo)

CATALOGUE PAGE & OTHERS

- [ex223001_1000.pdf](#) | PDF (0.13Mo)