

Product sheet



LCS³ LEGRAND

Optic Drawer modular with 12 multimode SC duplex connectors 19 inch 1U

REF. 032102 | EAN. 3414970961624

> [Visit e-catalogue](#)

Product characteristics

- 20° tilting for good internal view and access. End of travel stop.
- Supplied with 2 coiling kits, 2 cable glands and numbered labels
- Receive stackable pigtail cassette accessory up to 24 fibres.
- With 19 inch quick fixing solution for automatic mounting (no screws required)

Recommendation / Restriction

- To limit mechanical constraints on cables at drawer back, we recommend to use minimum 600mm depth cabinets. If less, you can use fibre panel ref. 032140.

The product's benefits

Installation

- This drawer is equipped with 19 inch quick fixing solution for automatic mounting (no screws required) and grounding. It offers 8 cable inputs, with dedicated space for direct clipping of fan-out if you choose preterminated trunks.

Usage


- This drawer offers scalability : easy move, add and change of blocks as you need.

Advantages

- Scalable : Easy move, add and change of blocks as you need
- With 19 inch quick fixing solution for automatic mounting (no screws required) and automatic grounding on 19" uprigh with conductive surface

Documentation

TECHNICAL DOCUMENTATION

-  S000099289EN-04.pdf | PDF (3.72Mo)
-  S000099289EN-05.pdf | PDF (3.74Mo)
-  LE09845AE.pdf | PDF (15.67Mo)
-  S000099289FR-05.pdf | PDF (3.73Mo)

Agreements & Certificates

-  LGRP-00694-V01.01-EN.pdf | PDF (0.61Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_1000.pdf | PDF (0.13Mo)

