

# Product sheet



LEGRAND

Domestic cartridge fuse - cylindrical type 10.3 x 38 - 32 A - without indicator

REF. 013332 | EAN. 3245060133320

[> Visit e-catalogue](#)

## Product characteristics

- Domestic cartridge fuses
- Cylindrical 10,3 x 38 - Rating : 32 Amps - Voltage ~ : 400 Volts - Rupture capacity Copper : 20000 Amps - Protected section : 6 mm<sup>2</sup> - Color Indication : Brown

## Documentation

### TECHNICAL DOCUMENTATION

 F00192EN-10.pdf | PDF (1.54Mo)

 F00192FR-10.pdf | PDF (1.54Mo)

### Agreements & Certificates

 NF-656079/A1 | (0.67Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0091.pdf | PDF (0.09Mo)