

Product sheet



LCS³ LEGRAND

Optic Drawer angled and modular 19 inch 1U to be equipped

REF. 032101 | EAN. 3414971420212

[> Visit e-catalogue](#)

Product characteristics

- Angled shape for cords management on sides
- To be equipped with 4 fibre optic blocks to reach up to 96 LC, 48 SC or 24 ST
- 20° tilting for good internal view and access. End of travel stop.
- Supplied with 2 coiling kits, 2 cable glands and numbered labels
- Receive stackable pigtail cassette accessory up to 24 fibres.

Recommendation / Restriction

- To limit mechanical constraints on cables at drawer back, we recommend to use minimum 600mm depth cabinets. If less, you can use fibre panel ref. 032140.

The product's benefits

Installation

- This drawer is equipped with 19 inch quick fixing solution for automatic mounting (no screws required) and grounding. It offers 8 cable inputs, with dedicated space for direct clipping of fan-out if you choose preterminated trunks.

Usage


- With this drawer, the space in the cabinet is optimized thanks to 1U saving with cords management on sides. Moreover this drawer offers scalability : easy move, add and change of blocks as you need.


Avantages

- Modular : Large choice of fibre optic blocks (LC, LC APC, SC, SC APC, ST, MTP) and many possible combinations, even mixing fibre and copper with the specific copper block for fibre optic drawer.
- With 19 inch quick fixing solution for automatic mounting (no screws required) and automatic grounding on 19" upright with conductive surface

Documentation

TECHNICAL DOCUMENTATION

 S000099289EN-04.pdf | PDF (3.72Mo)

 S000099289EN-05.pdf | PDF (3.74Mo)

CATALOGUE PAGE & OTHERS

 ex223001_1000.pdf | PDF (0.13Mo)



LE09845AE.pdf | PDF (15.67Mo)



S000099289FR-05.pdf | PDF (3.73Mo)