

Product sheet



LEGRAND

SPD - T2 - I_{max} 20 kA/pole - 1P

REF. 412220 | EAN. 3414970517944

[> Visit e-catalogue](#)

Product characteristics

- Class II (T2) low voltage SPDs - Protection against transient overvoltages for 230/400 V~ power networks (50/60 Hz). SPDs compliant with EN/IEC 61643 - 11 standards - Recommended for distribution boards
- T2 SPDs - SPDs with plug-in modules and status indicators : - Green : SPD operational - Orange : plug-in modules to be replaced
T2 - I_{max} 20 kA/pole - SPDs recommended for small installations - Up : 1.2 kV - I_n = 5 kA/pole - U_c : 320 V~ - Earthing systems : TT, TNC, TNS - Recommended MCB : DX³ 20 A - C curve - Number of poles : 1P - Remote status monitoring (FS contact) : No - Number of modules : 1

Documentation

TECHNICAL DOCUMENTATION

- F02060EN_05.pdf | PDF (0.62Mo)
- F02060FR_06.pdf | PDF (0.61Mo)
- EXB20026_TG_Surge_Protective_Devices_EN.pdf | PDF (8.37Mo)
- LE07561AA_6.pdf | PDF (0.53Mo)

CAD & Design specs / BIM

- 412220.dwg | DWG (0.18Mo)

CATALOGUE PAGE & OTHERS

- ex223001_0088-0089.pdf | PDF (0.16Mo)
- ex223001_0087.pdf | PDF (0.12Mo)
- ex223001_0085.pdf | PDF (0.07Mo)

Agreements & Certificates

- LGRP-2015-068-V1-EN.pdf | PDF (0.62Mo)
- OC / CB-AT 4283 | (0.27Mo)