

Product sheet



LEGRAND

RCBO - DX³ 6000 - 6 kA - 1P+N 230 V~ - 20 A - 30 mA
- A type - N left hand

REF. 411132 | EAN. 3414970751874

> [Visit e-catalogue](#)

Product characteristics

- RCBOs DX³ 6000 - 6 kA - residual current circuit breakers from 6 A to 32 A - A type - Conform to IEC 61009 - 1 - Compatible with prong - type supply busbars - Voltage dependent tripping - Breaking capacity : - 6000 - IEC 61009 - 1 - 6 kA / IEC 60947 - 2 for single pole + neutral - A type : detect AC and DC component faults - Enhanced immunity to unwanted tripping in disturbed environments - Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls
- Single pole + neutral - 230 V~ - Neutral on Left - hand side A Type 30 mA - C curve - Nominal rating In : 20 A - Number of modules : 1

Documentation

TECHNICAL DOCUMENTATION

→ [LE09580AA.pdf](#) | PDF (0.46Mo)

 [F02071EN-01.pdf](#) | PDF (0.66Mo)

CAD & Design specs / BIM

 [411121.dwg](#) | DWG (0.15Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0076-0077.pdf](#) | PDF (0.2Mo)

 [ex223001_0062.pdf](#) | PDF (0.08Mo)

Agreements & Certificates

 [OC / CB-689349/A1](#) | (0.53Mo)

 [LGRP-2015-267-v1-EN.pdf](#) | PDF (0.65Mo)