

# Product sheet



LEGRAND

Rigid conduit - with coupling - shock resistance 2 joules -  $\varnothing$  ext. 25 mm

REF. 651425 | EAN. 3245066514253

[> Visit e-catalogue](#)

## Product characteristics


- Rigid conduits Medium impact rigid conduits with integrated coupling - PVC without Pb, Sn, Cd (RoHS compliant) - Non flame propagating - Surface - mounting or flush-mounting - Suitable for prefabricated concrete - Conforming to European standard : EN/IEC 61386 - 21 - Crush resistance : 750 Newtons - Impact resistance : 2 joules at - 5 °C - Min operating t° : - 5 °C. Max operating t° : + 60 °C. IK 07 - Can be used outside - Supplied wrapped in film. Light grey (RAL 7035). Length of tubes : 3 m -  $\varnothing$  exterior : 25 mm -  $\varnothing$  interior : 21.4 mm - thickness : 1.80 mm

## Documentation

### TECHNICAL DOCUMENTATION

 [F01719EN-02.pdf](#) | PDF (0.17Mo)

### CATALOGUE PAGE & OTHERS

 [ex223001\\_0814.pdf](#) | PDF (0.35Mo)

 [ex223001\\_0815.pdf](#) | PDF (0.12Mo)