

# Product sheet



DPX<sup>3</sup> LEGRAND

Shunt release 200V-277V for DPX<sup>3</sup>160/250, DPX<sup>3</sup>-I 160/250 and DPX<sup>3</sup>/DPX<sup>3</sup>-I 160HP/250HP

REF. 421016 | EAN. 3245064210164

DPX<sup>3</sup>, auxiliary for moulded case circuit breaker and trip-free switch

> [Visit e-catalogue](#)

## Description

DPX<sup>3</sup>, auxiliary for moulded case circuit breaker and trip-free switch

### Product characteristics

- Allow remote tripping of a DPX<sup>3</sup>160, DPX<sup>3</sup>250, DPX<sup>3</sup>125HP, DPX<sup>3</sup>250HP, DPX<sup>3</sup>-I160, DPX<sup>3</sup>-I250, DPX<sup>3</sup>-I125HP, DPX<sup>3</sup>-I250HP
- Coil voltage 200 to 270V~/=
- Maximum power: 400 V~/W

## Documentation

### TECHNICAL DOCUMENTATION

- [Y4274F.pdf](#) | PDF (2.1Mo)
- [EXB22025\\_CA\\_DPX3\\_160-250\\_FR.pdf](#) | PDF (108.29Mo)
- [EXB16053\\_DPX3\\_160\\_250\\_EN.pdf](#) | PDF (107.63Mo)
- [EXB15015\\_TG\\_Coordination\\_EN.pdf](#) | PDF (5.41Mo)
- [EXB19026\\_CA\\_DPX3\\_125HP250HP\\_630\\_1600EN.pdf](#) | PDF (82.93Mo)
- [EXB21086\\_CA\\_DPX3HP125\\_250\\_DPX3630\\_1600FR.pdf](#) | PDF (83.49Mo)

### CATALOGUE PAGE & OTHERS

- [ex223001\\_0175.pdf](#) | PDF (0.08Mo)
- [ex223001\\_0165.pdf](#) | PDF (0.13Mo)

### Agreements & Certificates

- [LGRP-01584-V01.01-EN.pdf](#) | PDF (0.65Mo)