

# Product sheet



DLPLUS LEGRAND

Variable internal angle for DLPlus mini-trunking  
75x20mm

REF. 030301 | EAN. 3245060303013

[> Visit e-catalogue](#)

## Product characteristics

- Variable internal angle of 60 to 120 degrees
- Respect the protection index
- Improvement of aesthetics (covering of the cut)
- Colour: white

## The product's benefits

### Installation

- Clips directly on the body of the mini-trunking

### Usage

- Allows a neat and clean electrical installation finish

## Documentation

### TECHNICAL DOCUMENTATION

 [F00988EN-05.pdf](#) | PDF (2.71Mo)

 [F00988FR-03.pdf](#) | PDF (2.59Mo)

### Agreements & Certificates

 [LGRP-01603-V02.01-EN.pdf](#) | PDF (0.92Mo)

 [LGRP-01603-V02.01-FR.pdf](#) | PDF (0.88Mo)

### CATALOGUE PAGE & OTHERS

 [ex223001\\_1046.pdf](#) | PDF (0.12Mo)

 [ex223001\\_1048.pdf](#) | PDF (0.04Mo)