

Product sheet



DLP LEGRAND

Variable external angle for snap-on trunking
50x145mm

REF. 075634 | EAN. 3245060756345

> [Visit e-catalogue](#)

Product characteristics

- Variable external angle of 85 to 120 degrees
- Respect the protection index
- Improvement of aesthetics (covering of the cut)
- Composed with 2 elements for trunking 1 compartment, or 3 elements for trunking 2 compartments with partition junction
- Colour: white

Documentation

TECHNICAL DOCUMENTATION

 F00886FR-04.pdf | PDF (1.06Mo)

 F00886EN-06.pdf | PDF (1Mo)

 LE01001AB.pdf | PDF (0.41Mo)

CAD & Design specs / BIM

BIM-LEGRAND-GOULOTTES-BELGIQUE-2024.rvt | RVT (23.93Mo)

BIM-LEGRAND-TRUNKING-EXPORT-2024.rvt | RVT (14.36Mo)

BIM-LEGRAND-GOULOTTES-FRANCE-2024.rvt | RVT (13.17Mo)

The product's benefits

Installation

- Clips directly on the body of the trunking

Usage

- The external angles ensure the continuity of the flexible cover on the angles, hence preventing cut of cover and being aesthetic

CATALOGUE PAGE & OTHERS

 ex223001_1066-1067.pdf | PDF (0.17Mo)

 ex223001_1060.pdf | PDF (0.14Mo)

Agreements & Certificates

 LGRP-01604-V02.01-EN.pdf | PDF (0.74Mo)

 LGRP-01604-V02.01-FR.pdf | PDF (0.71Mo)