

# Product sheet



DLP LEGRAND

Variable external angle for snap-on trunking  
50x180mm

REF. 075636 | EAN. 3245060756369

> [Visit e-catalogue](#)

## Product characteristics

- Variable external angle of 85 to 120 degrees
- Respect the protection index
- Improvement of aesthetics (covering of the cut)
- Composed with 2 elements for trunking 1 compartment, or 3 elements for trunking 2 compartments with partition junction
- Colour: white

## The product's benefits

### Installation

- Clips directly on the body of the trunking

### Usage

- The external angles ensure the continuity of the flexible cover on the angles, hence preventing cut of cover and being aesthetic

## Documentation

### TECHNICAL DOCUMENTATION

→ [LE01002AB.pdf](#) | PDF (0.43Mo)

[F00886FR-04.pdf](#) | PDF (1.06Mo)

[F00886EN-06.pdf](#) | PDF (1Mo)

### CAD & Design specs / BIM

[BIM-LEGRAND-GOULOTTES-BELGIQUE-2024.rvt](#) | RVT (23.93Mo)

[BIM-LEGRAND-TRUNKING-EXPORT-2024.rvt](#) | RVT (14.36Mo)

[BIM-LEGRAND-GOULOTTES-FRANCE-2024.rvt](#) | RVT (13.17Mo)

### CATALOGUE PAGE & OTHERS

[ex223001\\_1066-1067.pdf](#) | PDF (0.17Mo)

[ex223001\\_1061.pdf](#) | PDF (0.13Mo)

### Agreements & Certificates

[LGRP-01604-V02.01-EN.pdf](#) | PDF (0.74Mo)

[LGRP-01604-V02.01-FR.pdf](#) | PDF (0.71Mo)