

Product sheet



LEGRAND

Pack of 100 Ø20 mm ISO end caps for Plexo³ cabinets

REF. 001956 | EAN. 3414971093119

[> Visit e-catalogue](#)

Product characteristics

- Plexo³ - IP 65 weatherproof cabinets, multifunction sleeves and Accessories - Self - extinguishing : resistance to incandescent wire 650°C. - Allows to achieve assemblies conform to IEC 61 439 - 3 - Weatherproof cabinets - IP 65 - IK 09 - Class II - Door and cabinet fully reversible. Removable chassis and faceplates from 2 - row versions up - 2 - position rail for modular products and moulded cases. Spacing between rails 150 mm - Can be fitted with perforated plates and solid faceplates for mounting non-modular products - Lockable door handle, sealable cover and faceplate - Shock - resistant polystyrene material - Box colour light grey L750A, cover colour dark grey R746A - Supplied without terminal blocks
- Accessories Direct piercing end caps - Pack consisting of 100 20 mm ISO end caps

Documentation

TECHNICAL DOCUMENTATION

 [EXB22026_CA_Plexo3_FR_imprimable.pdf](#) | PDF (33.87Mo)

 [EXB14046_CA_Plexo3_EN_print.pdf](#) | PDF (34.53Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0411.pdf](#) | PDF (0.08Mo)

 [ex223001_0413.pdf](#) | PDF (0.04Mo)

 [ex223001_0412.pdf](#) | PDF (0.11Mo)