

Product sheet



VIKING 3 LEGRAND

Protection conductor terminal block, screw connection, 1 connection 1entry/1outlet, Cross-section 35mm² - green/yellow

REF. 037175 | EAN. 3245060371753

[> Visit e-catalogue](#)

Product characteristics

- Green/yellow terminal blocks are recommended for protection conductors.
- 2 areas for automatic insertion bridging combs up to 8mm pitch (upper level only for multi-level terminal blocks)
- Easy insertion of conductors thanks to the ergonomic shape of the entry and outlet.

Recommendation / Restriction

- Installation recommended for electrical connection in industrial and tertiary cabinets and enclosures.

The product's benefits

Installation

- A securing pin on the insulating body holds the Viking 3 terminal blocks together for ease of handling and perfect alignment on the rail. The assembly/disassembly of a terminal block is still possible without removing the adjacent terminal blocks

Usage

- Terminal blocks have two marking zones per level allowing a clear, visible and convenient identification of the circuit. Compatible with CAB 3 marking systems.

Documentation

TECHNICAL DOCUMENTATION

- F00671EN-02.pdf | PDF (1.11Mo)
- F00914FR-01.pdf | PDF (0.66Mo)
- F00914FR-00.pdf | PDF (1.06Mo)
- F00914EN-01.pdf | PDF (0.66Mo)
- F00671FR-02.pdf | PDF (1.08Mo)
- F00914EN-00.pdf | PDF (0.87Mo)

CAD & Design specs / BIM


- 037175.dwg | DWG (0.14Mo)

CATALOGUE PAGE & OTHERS

- ex223001_0458.pdf | PDF (0.16Mo)
- ex223001_0465.pdf | PDF (0.06Mo)
- ex223001_0466.pdf | PDF (0.13Mo)

Agreements & Certificates

- Ex-002/i | (0.25Mo)

-  UL recogn-20101029-E60900 | (0.13Mo)
-  NF App Industri-NF208_1008 | (0.28Mo)
-  IMQ-CA02.03545 | (0.74Mo)
-  ATEX-LCIE 16 ATEX 3049U - 02 | (0.71Mo)
-  VERITAS (BV)-23393/C0 BV | (0.61Mo)