


Product sheet



LEGRAND

Reversible curved glass door XL³ 4000 - width 725 mm
- Height 2000 mm

REF. 020564 | EAN. 3245060205645

[> Visit e-catalogue](#)


Product characteristics

- Distribution enclosures XL³ 4000 - IP 30 - IK 07 - IP 55 - IK 08 with door and sealing kit for use when joining enclosures - Consist of the combination of a "roof - base" assembly, structural uprights, functional uprights, rear and side panels RAL 7035, plinths RAL 7004 - Height 2000 or 2200 mm. - Capacity 24 modules (enclosures width 725 or width 975 with internal cable sleeve), 36 modules (enclosures width 975) - Usable faceplate height 1800 mm (1700 mm only if using the pivoting support frame) or 2000 mm
- Reversible doors - Supplied with handle - Interchangeable key barrels, to be ordered separately - For mounting on Front, rear or side Curved - glass - Width 725 mm - Height : 2000 mm


Documentation

TECHNICAL DOCUMENTATION


→ [F0996C-02.pdf](#) | PDF (0.37Mo)

 [EXB15002_CA_XL3-4000-6300_EN.pdf](#) | PDF (51.43Mo)

Agreements & Certificates

 [LOVAG-IT 12.017](#) | (0.13Mo)

 [LOVAG-IT 12.019](#) | (0.59Mo)

 [LOVAG-IT 13.045](#) | (0.12Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0381.pdf](#) | PDF (0.46Mo)