

Product sheet



LEGRAND

Internal door - for cabinets height 400 x width 300 - height 341 x width 236 mm

REF. 036359 | EAN. 3245060363598

[> Visit e-catalogue](#)

Product characteristics

- Atlantic stainless steel and Marina cabinets - internal doors
- Insulating internal doors RAL 7035 - For direct mouting in Marina cabinets , with Cat.No 0 363 69 in Atlantic metal cabinets - IP XXB - Polyester fiber glass reinforced, height 4 mm - Self - extinguishing 960°C acc. to IEC EN 60695 - 2 - 11 - Grid lines integrated on back - Centre marking on Front - Adjustable distance between cabinet door and internal door : 42 to 50 mm for Atlantic cabinets , more than 100 mm for Marina cabinets - Right or Left opening, captive hinge pins - Double bar key : 1 key for 400 to 600 mm height, 2 keys for height from 700 mm - Take key barrels and other barrels - For cabinets Height x Width : 400 x 300 mm - Dim. Height x Width : 341 x 236 mm - Usable dim. Height x Width : 306 x 205 mm

Documentation


TECHNICAL DOCUMENTATION

→ [041728-00.pdf](#) | PDF (0.74Mo)

CAD & Design specs / BIM

 [036359.dwg](#) | DWG (0.05Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0436.pdf](#) | PDF (0.2Mo)