

Product sheet



MOSAIC™ LEGRAND

Lighting management-power pack-ceiling mounting-2 outputs-1x16 A+dry contact

REF. 048850 | EAN. 3245060488505

[> Visit e-catalogue](#)

Product characteristics

- 2 x 16 A outputs
- 1 sensor input, 2 inputs for auxiliaries
- Connection via screw terminals

Recommendation / Restriction

- Connection to sensors (Cat.Nos 0 488 20/22/34 and 0 784 85/86, 5 740 46/48) by cord or RJ 45 cable or BUS/SCS cable to be fitted with RJ 45 connector Cat.No 0 488 72
- 2 x 16 A outputs
- 1 sensor input, 2 inputs for auxiliaries

The product's benefits

Installation

- Addressing methods using sensors and control units: automatic configuration custom configuration by pressing the "Learn" button on the product

Usage

- For controlling 1 or 2 circuits in one room - Used to control 2 ON/OFF lighting circuits or 1 lighting circuit + 1 ventilation circuit

Avantages

- Combining a sensor and room controller provides additional functions: dimming control and blinds / HVAC control
- Can be controlled for each output by a sensor and/or an individual BUS control unit

Documentation

TECHNICAL DOCUMENTATION

- S000107192EN-1.pdf | PDF (0.55Mo)
- LE07602AA.pdf | PDF (9.21Mo)
- LE03080AC.pdf | PDF (0.38Mo)
- S000107192FR-1.pdf | PDF (0.55Mo)

Agreements & Certificates

- LGRP-00077-V01.01-EN.pdf | PDF (0.56Mo)

CAD & Design specs / BIM

- Legrand_Gestion_eclairage_Actionneur.rfa | RFA (0.53Mo)
- Legrand_Lighting_Management_Actuator.rfa | RFA (0.54Mo)



KSC-JW02001-13002 | (0.26Mo)