

Product sheet



LEGRAND

Cam switch - 3-phase motor switch starter 1 way,2 speed O-PV-GV - PR 12 - box

REF. 027772 | EAN. 3245060277727

[> Visit e-catalogue](#)

Product characteristics

- Cam switches insulating box - For selecting and changing the status of the circuits into which it is integrated - For viewing the state of equipment according to the position of the selector lever - Boxed device, class II - Contacts with positive opening and double breaking of poles - Presentation : black or grey/black selector lever, faceplate with marking - Conform to standards IEC EN 60947 - 3 - IP 65 for 76 x 76 and 96 x 120 mm boxes - IP 55 for 135 x 170 mm boxes
- Function : 3 - phase motor switch Starter 1 way, 2 speed Dalhander - Range : PR 12 - Max. rating AC 3 : 4 kW - Number of contacts : 8

Documentation

TECHNICAL DOCUMENTATION

→ [096897001-01.pdf](#) | PDF (0.72Mo)

CATALOGUE PAGE & OTHERS

[ex223001_0490.pdf](#) | PDF (0.08Mo)

[ex223001_0492-0493.pdf](#) | PDF (0.37Mo)

[ex223001_0491.pdf](#) | PDF (0.04Mo)

Agreements & Certificates

[UL recogn-280206-E57817](#) | (0.18Mo)

[OC / CB-FR 60026094B](#) | (0.32Mo)

[CSA-1725160](#) | (0.1Mo)