

Product sheet



LEGRAND

Roof base for cable sleeves XL³ 4000 - depth 975 mm - width 475 mm

REF. 020503 | EAN. 3245060205034







[> Visit e-catalogue](#)

Product characteristics

- Distribution enclosures XL³ 4000 - IP 30 - IK 07 - IP 55 - IK 08 with door and sealing kit for use when joining enclosures - Consist of the combination of a "roof - base" assembly, structural uprights, functional uprights, rear and side panels RAL 7035, plinths RAL 7004 - Height 2000 or 2200 mm. - Capacity 24 modules (enclosures width 725 or width 975 with internal cable sleeve), 36 modules (enclosures width 975) - Usable faceplate height 1800 mm (1700 mm only if using the pivoting support frame) or 2000 mm
- Enclosures and cable sleeves modular metal Roof - base for cable sleeves - Fitted with cable entry plates - Take the structural up Rights - Depth : 975 mm - Width external : 475 mm - Width usable : 350 mm

Documentation

TECHNICAL DOCUMENTATION



-  EXB22009_Flipbook_FR_(03_2022).pdf | PDF (6.2Mo)
-  F00254FR-05.pdf | PDF (0.67Mo)
-  F00254EN-04.pdf | PDF (0.56Mo)
-  EXB15002_CA_XL3-4000-6300_EN.pdf | PDF (51.43Mo)
-  EXB22010_Flipbook_EN_(03_2022).pdf | PDF (6.56Mo)
-  F0998K.pdf | PDF (1.8Mo)

CAD & Design specs / BIM



Legrand_Armoire_XL³_4000_gaine_à_câble.rfa | RFA (0.51Mo)

Legrand_Distribution_enclosure_XL³_4000_external_cables_sleeves.rfa | RFA (0.51Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0380.pdf | PDF (0.14Mo)
-  ex223001_0383.pdf | PDF (0.08Mo)

Agreements & Certificates

-  LOVAG-IT 13.045 | (0.12Mo)
-  LOVAG-IT 12.017 | (0.13Mo)
-  LOVAG-IT 12.019 | (0.59Mo)