

Product sheet



LEGRAND

Roof - for Marina enclosures width 800 x depth 400 mm

REF. 036297 | EAN. 3245060362973

[> Visit e-catalogue](#)

Product characteristics

- Marina enclosures - polyester - IP 66 - IK 10 - IP 66 acc. to IEC EN 60529, LCIE n° 60059283 - 560528 - IK 10 acc. to EN 62262 (EN 50102) - Class II (Used to create totally isolated assemblies acc. to EN 60439 - 1) - Fiberglass reinforced polyester. Self-extinguishing 960°C acc. to IEC EN 60695 - 2 - 11 - Adapted to corrosive environment. Supplied with Fixing kit for plain plates or sectioned uprights - Depth adjustment of equipment - Equipped with low cable entries plate - Reversible door with strand holder - 3 point closing with handle fitted with 1/2 locking latch 2433 A (other key code, please consult us) - Stainless steel hinges and hinges axis
- Roof RAL 7035 - For enclosure width 800 x depth 400 mm

Documentation

TECHNICAL DOCUMENTATION

→ [041653-00.pdf](#) | PDF (0.22Mo)

CAD & Design specs / BIM

 [036297.dwg](#) | DWG (0.04Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0424.pdf](#) | PDF (0.12Mo)

 [ex223001_0428.pdf](#) | PDF (0.39Mo)

 [ex223001_0426-0427.pdf](#) | PDF (0.36Mo)