

Product sheet



LEGRAND

Roof for Atlantic metal cabinet - steel - width 400 mm
x depth 200 mm - RAL 7035

REF. 036552 | EAN. 3245060365523

> [Visit e-catalogue](#)

Product characteristics

- Atlantic metal cabinets supplied with plain plate - IP 55/IP 66 - IK 10 - Type 4x - Type 12 - IP 66 according to standards IEC EN 60529 for 1 - door cabinets - IP 55 according to standards IEC EN 60529 for 2 - door cabinets - IK 10 according to standards IEC EN 62262 - LCIE 17 07 90 10A - Type 4x, 1 door, Type 12, 2 doors - cULus, Bureau Veritas - EMC attenuation 20 dB (for an EMC attenuation from 40 to 50 dB at 1 GHz, please consult us) - Excellent resistance to corrosion and chemical agents - 80 m thick textured polyester coating. Anti - corrosion treatment for hinges and pins - Reversible door - Fitted with lever - Supplied with double bar lock - Self - centering positioning system for the equipment - Compatible with all Atlantic Accessories Low cable entries RAL 7035 - Optional depth adjustment for cabinets 400 mm depth, with slide rails Cat.No 0 367 45
- Roofs RAL 7035 - Steel - Possible adjustment ± 20 mm (Front or back) - For cabinets Width : 400 mm - For cabinets Depth : 200 mm - Weight : 1.4 kg

Documentation

TECHNICAL DOCUMENTATION

→ [LE08579AA-00.pdf](#) | PDF (0.46Mo)

CAD & Design specs / BIM

 [036552.dwg](#) | DWG (0.04Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0420-0421.pdf](#) | PDF (0.28Mo)

 [ex223001_0416.pdf](#) | PDF (0.06Mo)