

Product sheet



MOSAIC™ LEGRAND

TV socket Mosaic - TV/R/SAT - screened - insulated - 2 modules - white

REF. 078786 | EAN. 3245060787868

[> Visit e-catalogue](#)

Product characteristics

- Mosaic™ Programm e mechanisms - television sockets - For DVBT, Cablecast and satellite installation - UHD TV compatible - Class A shielded star sockets LTE Ready (4G protected) Recomm ended coaxial cable : 17 VATC - Star cabling (1 socket = 1 cable to antenna, splitter or multiswitch) Visual checking of the connection - Meet EN 50083 - 4 and EN 50083 - 2 European directive - TV : male connector (Ø9.5 mm) - 5 - 68 / 120 - 862 MHz - R : female connector (Ø9.5 mm) - 87.5 - 108 MHz - SAT : "F type" connector - 950 - 2400 MHz
- Multi TV star sockets TV - R - SAT - 2 modules - Low attenuation : 1.5 dB - White - Can be installed in receptacles for floor sockets

Documentation

TECHNICAL DOCUMENTATION

- [LE08365AA.pdf](#) | PDF (1.54Mo)
- [S000092510FR-04.pdf](#) | PDF (0.8Mo)
- [S000092510EN-04.pdf](#) | PDF (0.79Mo)

CAD & Design specs / BIM

- [BIM-LEGRAND-MOSAIC-2023-ENGLISH.rvt](#) | RVT (126.68Mo)
- [BIM-LEGRAND-MOSAIC-2023-FRANCAIS.rvt](#) | RVT (128.48Mo)

CATALOGUE PAGE & OTHERS

- [ex223001_0877.pdf](#) | PDF (0.08Mo)
- [ex223001_1191.pdf](#) | PDF (0.1Mo)