

# Product sheet



MOSAIC™ LEGRAND

TV star socket Mosaic - TV-R-SAT - SAT - 2 modules - white

REF. 078794 | EAN. 3414970764928

> [Visit e-catalogue](#)

## Product characteristics

- Mosaic™ Programm e mechanisms - television sockets - For DVBT, Cablecast and satellite installation - UHD TV compatible - Class A shielded star sockets LTE Ready (4G protected) Recomm ended coaxial cable : 17 VATC - Star cabling (1 socket = 1 cable to antenna, splitter or multiswitch) Visual checking of the connection - Meet EN 50083 - 4 and EN 50083 - 2 European directive - TV : male connector (Ø9.5 mm ) - 5 - 68 / 120 - 862 MHz - R : female connector (Ø9.5 mm ) - 87.5 - 108 MHz - SAT : "F type" connector - 950 - 2400 MHz
- Multi TV star sockets TV - R - SAT - SAT 2 modules - White - (In 1 TV - R - SAT / In 2 SAT 2) - Low attenuation : 1.5 dB - Can be installed in receptacles for floor sockets

## Documentation

### TECHNICAL DOCUMENTATION

- [LE08365AA.pdf](#) | PDF (1.54Mo)
- [F03268FR-00.pdf](#) | PDF (0.4Mo)
- [F03268EN-00.pdf](#) | PDF (0.4Mo)

### CAD & Design specs / BIM

- [BIM-LEGRAND-MOSAIC-2023-ENGLISH.rvt](#) | RVT (126.68Mo)
- [BIM-LEGRAND-MOSAIC-2023-FRANCAIS.rvt](#) | RVT (128.48Mo)

### CATALOGUE PAGE & OTHERS

- [ex223001\\_0877.pdf](#) | PDF (0.08Mo)
- [ex223001\\_1191.pdf](#) | PDF (0.1Mo)