

Product sheet



MOSAIC™ LEGRAND

TV socket Mosaic - single - male Ø9.52 mm - 2 modules - alu

REF. 079292 | EAN. 3245060792923


[> Visit e-catalogue](#)

Product characteristics


- Mosaic™ Programm e mechanisms - television sockets - For DVBT, Cablecast and satellite installation - UHD TV compatible - Class A shielded star sockets LTE Ready (4G protected) Recomm ended coaxial cable : 17 VATC - Star cabling (1 socket = 1 cable to antenna, splitter or multiswitch) Visual checking of the connection - Meet EN 50083 - 4 and EN 50083 - 2 European directive - TV : male connector (Ø9.5 mm) - 5 - 68 / 120 - 862 MHz - R : female connector (Ø9.5 mm) - 87.5 - 108 MHz - SAT : "F type" connector - 950 - 2400 MHz
- Single TV star sockets - Low attenuation : 1 dB TV 9.5 mm male - Alu - 2 modules - Can be installed in receptacles for floor sockets

Documentation

TECHNICAL DOCUMENTATION

 S000090598EN-02.pdf | PDF (0.33Mo)

 LE08364AA.pdf | PDF (1.51Mo)

 S000090598FR-02.pdf | PDF (0.33Mo)

CAD & Design specs / BIM

BIM-LEGRAND-MOSAIC-2023-ENGLISH.rvt | RVT (126.68Mo)

BIM-LEGRAND-MOSAIC-2023-FRANCAIS.rvt | RVT (128.48Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0877.pdf | PDF (0.08Mo)

 ex223001_1191.pdf | PDF (0.1Mo)

Agreements & Certificates

 LGRP-00561-V01.01-FR.pdf | PDF (0.64Mo)