

Product sheet



NILOÉ™ LEGRAND

TV single star socket Niloé - 9.5 male - attenuation 1 dB - white

REF. 764551 | EAN. 3414970683229

[> Visit e-catalogue](#)

Product characteristics

- Nilo - television star sockets - Mechanisms supplied with cover plates and support frames. To be equipped with plates . Fixing with screws or claws (supplied) - For DVBT, Cablecast and satellite installation. UHD TV compatible. Class A shielded star sockets LTE Ready (4G protected). - Recomm ended coaxial cable : 17 VATC. Star cabling (1 socket = 1 cable to antenna, splitter or multiswitch). Visual checking of the connection - Meet EN 50083 - 4 and EN 50083 - 2 European directive. Low attenuation : less than 1 dB - TV : male connector (9.5 mm) - R : female connector (9.5 mm) - SAT : "F type" connector - TV : 5 - 68 / 120 - 862 MHz - R : 87.5 - 108 MHz - SAT : 950 - 2400 MHz
- Single TV star sockets - Low attenuation : 1 dBTV - 9.5 male - White

Documentation

TECHNICAL DOCUMENTATION

- [LE08364AA.pdf](#) | PDF (1.51Mo)
-  [S000093616FR-00.pdf](#) | PDF (2.36Mo)
-  [S000093616EN-00.pdf](#) | PDF (2.36Mo)

CATALOGUE PAGE & OTHERS

-  [ex223001_0747.pdf](#) | PDF (0.1Mo)