

# Product sheet



SYNERGY™ LEGRAND

TV-R-SAT socket Synergy - "F" type - white

REF. 730043 | EAN. 3245067300435

[> Visit e-catalogue](#)

## Product characteristics

- Synergy - telephone, data and TV sockets - white - Front plates : white thermoset - Terminal screws captive and backed off ready for cabling - large angled terminal entries - Compact mechanism for maximised wiring space - Supplied with faceplate screw caps
- TV sockets - For DVBT, Cablecast and satellite installation. UHD TV compatible - Class A shielded star sockets LTE Ready (4G protected) . Recommended coaxial cable : 17 VATC. Star cabling (1 socket = 1 cable to antenna, splitter or multiswitch) . Visual checking of the connection - Meet EN 50083 - 4 and EN 50083 - 2 European directive - TV : male connector (9.5 mm) - R : female connector (9.5 mm) - TV : 5 - 68 / 120 - 862 MHz - R : 87.5 - 108 MHz - SAT : 950 - 2400 MHz - 2 modules Multi TV star sockets - TV - R - SAT - Low attenuation : less than 1.5 dB

## Documentation

### TECHNICAL DOCUMENTATION

 F00241EN-00.pdf | PDF (0.24Mo)

 0064FV6-02.pdf | PDF (0.53Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0718.pdf | PDF (0.09Mo)