

# Product sheet



LEGRAND

Cable glands metal - IP 68 - ISO 25 - Clamping capacity diameter 8-16 mm

REF. 095505 | EAN. 3245060955052

[> Visit e-catalogue](#)

## Product characteristics

- Metal cable glands IP 68 - ISO and PG
- Metal cable glands - Mechanically tightened cable glands with neoprene weatherproof seal for IP 68 protection. - Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength - Supplied with surface seal mounted ISO - Conform to EN 50262 - ISO : 25 - Clamping capacity Min. : 8 mm - Clamping capacity Max. : 16 mm

## Documentation

### TECHNICAL DOCUMENTATION

 F02550FR00.pdf | PDF (2.13Mo)

### CAD & Design specs / BIM

 095505.dwg | DWG (0.06Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0445.pdf | PDF (0.06Mo)

### Agreements & Certificates

 LGRP-2014-115-V1-EN.pdf | PDF (0.96Mo)