

# Product sheet



LEGRAND

Cable gland plastic - IP 68 - ISO 20 - clamping capacity 8-12 mm - RAL 7001

REF. 098003 | EAN. 3245060980030

[> Visit e-catalogue](#)

## Product characteristics

- Cable glands with clamping capacity for cable diameter 8 to 12 mm
- Supplied with surface seal and locking nut mounted
- Conform to EN 62 444
- Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength
- Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength

## Documentation

### TECHNICAL DOCUMENTATION

 F03595FR-01.pdf | PDF (1.11Mo)

 F03595EN-01.pdf | PDF (1.19Mo)

### CAD & Design specs / BIM


 098003.dwg | DWG (0.12Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0447.pdf | PDF (0.06Mo)

 ex223001\_0446.pdf | PDF (0.07Mo)

### Agreements & Certificates

 OC / CB-IT-23350 | (0.64Mo)

 OC / CB-FR\_711319 | (0.68Mo)

 OC / CB-FR\_711334 | (0.59Mo)

 NF-NF012\_3289/A1 | (0.69Mo)

 IMQ-CA02.06749 | (0.56Mo)

 VDE-40023632 | (2.52Mo)

 OC / CB-FR\_714769/A1 | (0.63Mo)

 NF-NF012\_2897 | (0.8Mo)