

Product sheet



PLEXO™ LEGRAND

Square Plexo box with 7 direct entry membrane glands
- IP55 IK07 - 80x80x45 mm - white RAL 9010

REF. 092013 | EAN. 3245060920135

[> Visit e-catalogue](#)

Product characteristics

- Plexo boxes IP 55 - IK 07 - with direct entry membrane glands - 650°C - IP 55 - IK 07 - Resistance to incandescent wire 650°C - For use as junction boxes in any type of normal installation circuit - Operating temperature : - 25 to +40°C - Interchangeable membrane glands with direct entries for IRL tubes up to 16 and R02V cables, with marked cut - out for IRL tube greater than 16 - Captive cover with tie. Space for marking on both sides of the cover. Fixing with vertical level adjustment. Class II is ensured by protective caps (supplied) for the Fixing screws - boxes without halogenated flame retardants (European Directive RoHS 2002/95/EC)
- Square boxes - Can be fixed using a tool such as a Pulsa 700 E nail gun - 7 membrane glands 65 x 65 x 40 mm - White RAL 9010 - Accepted cable and tube : 4 to 20 mm - Clippable covers

Documentation

TECHNICAL DOCUMENTATION

 F01039EN-03.pdf | PDF (1.16Mo)

 F01039FR-03.pdf | PDF (1.19Mo)

Agreements & Certificates

 LGRP-01610-V01.01-FR.pdf | PDF (0.57Mo)

 OC / CB-FR_715099 | (0.51Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0801.pdf | PDF (0.1Mo)