

Product sheet



LEGRAND

Cable gland plastic - IP 68 - ISO 32 - clamping capacity 19-25 mm - RAL 7001

REF. 098006 | EAN. 3245060980061

[> Visit e-catalogue](#)

Product characteristics

- Cable glands with clamping capacity for cable diameter 19 to 25 mm
- Supplied with surface seal and locking nut mounted
- Conform to EN 62 444
- Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength
- Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength


Documentation

TECHNICAL DOCUMENTATION

 F03595FR-01.pdf | PDF (1.11Mo)


 F03595EN-01.pdf | PDF (1.19Mo)

CAD & Design specs / BIM


 098006.dwg | DWG (0.12Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0446.pdf | PDF (0.07Mo)

 ex223001_0447.pdf | PDF (0.06Mo)

Agreements & Certificates

 OC / CB-IT-23350 | (0.64Mo)

 IMQ-CA02.06749 | (0.56Mo)

 VDE-40010044 | (0.36Mo)