

Product sheet



PLEXO™ LEGRAND

Square Plexo box with 7 direct entry membrane glands
- IP55 IK07 - 80x80x45 mm - grey/red RAL 7035/3000

REF. 092015 | EAN. 3245060920159

[> Visit e-catalogue](#)

Product characteristics

- Plexo boxes IP 55 - IK 07 - with direct entry membrane glands - 960 °C - Resistance to incandescent wire : 960°C - Junction boxes for safety circuit installations in buildings open to the public and work premises - Operating temperature : - 25 to +40°C - Interchangeable membrane glands with direct entry for IRL tubes up to 16 and R02V cables. Marked cut - out for IRL tubes greater than 16 - Captive cover with clippable tie between box and cover - Space for marking on both sides of the cover of 80 x 80 and 105 x 105 boxes - Fixing with vertical level adjustment - Class II is ensured by protective caps (supplied) for the Fixing screws
- Square boxes - Grey/red RAL 7037/300080 x 80 x 45 mm - Clippable covers - 7 membrane glands (Cat.No 0 919 09) - Accepted cable and tube : 4 to 20 mm

Documentation

TECHNICAL DOCUMENTATION

 F00893FR-01.pdf | PDF (0.98Mo)

 F00893EN-01.pdf | PDF (0.98Mo)

Agreements & Certificates

 OC / CB-FR_715099 | (0.51Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0804-0805.pdf | PDF (0.32Mo)

 ex223001_0802.pdf | PDF (0.07Mo)