

# Product sheet



PLEXO™ LEGRAND

Box Plexo - IP 55 - IK 07 - 310x240x124 - 24 entry membrane glands

REF. 092082 | EAN. 3245060920821

[> Visit e-catalogue](#)

## Product characteristics

- Plexo™ boxes IP 55 - IK 07 - with direct entry membrane glands - 750 °C - Resistance to glow wire test : 750 °C (EN 60695 2 - 11) - Operating temperature : - 25 °C to + 40 °C - Interchangeable membrane glands with direct entry - Captive cover with clippable tie between box and cover except boxes 310 x 240 and 360 x 270 - Cover opens/closes with a 1/4 turn of a regular screwdriver, marking 0 and I - Class II is ensured by protection caps (supplied) for the attachment screws Rectangular boxes - Grey RAL 7035 310 x 240 x 124 mm - 24 glands - Ø cables and tubes accepted 4 to 40 mm

## Documentation

### TECHNICAL DOCUMENTATION

[fa343afr.pdf](#) | PDF (0.03Mo)

### Agreements & Certificates

[LGRP-01611-V01.01-EN.pdf](#) | PDF (1.06Mo)

[LGRP-01611-V01.01-FR.pdf](#) | PDF (0.57Mo)

### CATALOGUE PAGE & OTHERS

[ex223001\\_0804-0805.pdf](#) | PDF (0.32Mo)

[ex223001\\_0802.pdf](#) | PDF (0.07Mo)