

# Product sheet



## LEGRAND

Metal faceplate XL<sup>3</sup> 800/4000 - DPX<sup>3</sup>/DPX-IS - captive screws - 36 modules

REF. 020960 | EAN. 3245060209605



[> Visit e-catalogue](#)

## Product characteristics


- Equipment for XL<sup>3</sup> 4000 - for mounting on adjustable plate : DPX<sup>3</sup> 160, DPX<sup>3</sup> 250 fixed version
- Metal faceplates for devices In =ertical position For DPX<sup>3</sup> with or without motor driven handle - 36 modules - Hinges Cat.No 0209 59 available as an option - With captive screws

## Documentation








### TECHNICAL DOCUMENTATION

-  EXB15002\_CA\_XL3-4000-6300\_EN.pdf | PDF (51.43Mo)
-  LE05187AA.pdf | PDF (0.42Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_0387.pdf | PDF (0.06Mo)
-  ex223001\_0384.pdf | PDF (0.22Mo)
-  ex223001\_0385.pdf | PDF (0.12Mo)

### Agreements & Certificates

-  LOVAG-IT 12.067 | (0.55Mo)
-  LOVAG-IT 12.073 | (0.58Mo)
-  LOVAG-IT 12.017 | (0.13Mo)
-  LOVAG-IT 12.019 | (0.59Mo)
-  LGRP-2011-079-V1-FR.pdf | PDF (0.18Mo)
-  LOVAG-IT 12.075 | (0.58Mo)
-  LOVAG-IT 12.074 | (0.59Mo)