

# Product sheet



PLEXO™ LEGRAND

Square Plexo box with 7 direct entry membrane glands  
- IP55 IK07 - 105x105x55 mm - grey/red RAL  
7035/3000

REF. 092025 | EAN. 3245060920258

[> Visit e-catalogue](#)

## Product characteristics

- Plexo boxes IP 55 - IK 07 - with direct entry membrane glands - 960 °C - Resistance to incandescent wire : 960°C - Junction boxes for safety circuit installations in buildings open to the public and work premises - Operating temperature : - 25 to +40°C - Interchangeable membrane glands with direct entry for IRL tubes up to 16 and R02V cables. Marked cut - out for IRL tubes greater than 16 - Captive cover with clippable tie between box and cover - Space for marking on both sides of the cover of 80 x 80 and 105 x 105 boxes - Fixing with vertical level adjustment - Class II is ensured by protective caps (supplied) for the Fixing screws
- Square boxes - Grey/red RAL 7037/3000 105 x 105 x 55 mm - Cover closed with a 1/4 turn - Fixed using 2 internal points (screws with max. 5 mm ) or 3 points outside the wiring space (screws with max. 4 mm ) - 7 membrane glands (Cat.No 0 919 01) - Accepted cable and tube : 4 to 25 mm

## Documentation

### TECHNICAL DOCUMENTATION

 F00893FR-01.pdf | PDF (0.98Mo)


 F00893EN-01.pdf | PDF (0.98Mo)

### Agreements & Certificates

 OC / CB-FR\_715099 | (0.51Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0804-0805.pdf | PDF (0.32Mo)

 ex223001\_0802.pdf | PDF (0.07Mo)