

# Product sheet



NILOÉ™ LEGRAND

TV-R-SAT terminal socket Niloé - attenuation -10 dB - ivory

REF. 764665 | EAN. 3414970685162




[> Visit e-catalogue](#)

## Product characteristics

- Nilo - television passthrough and terminal sockets - Mechanisms supplied with cover plates and support frames. To be equipped with plates . Fixing with screws or claws (supplied) - Installation in case of maintenance. An amplifier and a line balancing are recommended - TV : male connector (9.5 mm ) - R : female connector (9.5 mm ) - SAT : "F type" connector - Recommended coaxial cable : 17 VATC - Visual checking of the connection - TV : 5 - 68 / 120 - 862 MHz - R : 87.5 - 108 MHz - SAT : 950 - 2400 MHz
- Terminal sockets - 1 input with 1 resistance cap socket - Attenuation : - 10 dBTV - R - SAT - Ivory

## Documentation

### TECHNICAL DOCUMENTATION

-  S000093614EN-00.pdf | PDF (3.02Mo)
-  LE08472AA.pdf | PDF (1.62Mo)
-  S000093614FR-00.pdf | PDF (3.03Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_0746.pdf | PDF (0.1Mo)