

Product sheet



NILOÉ™ LEGRAND

TV-R-SAT-SAT multiple star socket Niloé - attenuation 1.5 dB - ivory

REF. 764666 | EAN. 3414970685193

[> Visit e-catalogue](#)

Product characteristics

- Nilo - television star sockets - Mechanisms supplied with cover plates and support frames. To be equipped with plates . Fixing with screws or claws (supplied) - For DVBT, Cablecast and satellite installation. UHD TV compatible. Class A shielded star sockets LTE Ready (4G protected). - Recomm ended coaxial cable : 17 VATC. Star cabling (1 socket = 1 cable to antenna, splitter or multiswitch). Visual checking of the connection - Meet EN 50083 - 4 and EN 50083 - 2 European directive. Low attenuation : less than 1 dB - TV : male connector (9.5 mm) - R : female connector (9.5 mm) - SAT : "F type" connector - TV : 5 - 68 / 120 - 862 MHz - R : 87.5 - 108 MHz - SAT : 950 - 2400 MHz
- Multiple TV star sockets TV - R - SAT - SAT - Low attenuation : 1.5 dB - In 1 : TV - R - SAT 1 / In 2 : SAT 2 - Ivory

Documentation

TECHNICAL DOCUMENTATION

 S000093617FR-01.pdf | PDF (1.42Mo)

 S000093617EN-01.pdf | PDF (1.42Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0747.pdf | PDF (0.1Mo)