

Product sheet



SYNERGY™ LEGRAND

Sinergy Sleek Cable outlet 20A - Brushed Stainless steel

REF. 832019 | EAN. 3414970660541

[> Visit e-catalogue](#)

Product characteristics

- 20A 250V~
- Screw type terminals for enhanced contacts
- Marked terminals for easy identification
- Screwless cover plate is square 86x86 mm, product thickness is 4mm (once is installed onto the wall).
- Complete product, cover plates are clipped onto the mechanism itself.

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Terminal screws backed off ready to cabling

Usage

- Aesthetic solution for devices requesting hard-wiring connection

Avantages

- Plate in austenitic stainless steel Non magnetic Grade 304L
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

 [F02359EN-00.pdf](#) | PDF (0.09Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0730.pdf](#) | PDF (0.09Mo)