

Product sheet



SYNERGY™ LEGRAND

Synergy™ Authentic - Cable outlet 45A - Polished Stainless Steel

REF. 833226 | EAN. 3414970666345

[> Visit e-catalogue](#)

Product characteristics

- 45A, 250V~
- Screw type terminals for enhanced contacts
- Marked terminals for easy identification
- Cover plate is square 86x86 mm, product thickness is 7mm (once is installed onto the wall).
- Monobloc complete product = ready-to-install product

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Terminal screws backed off ready to cabling

Usage

- Aesthetic solution for devices requesting hard-wiring connection

Avantages


- Plate in Stainless steel rust resistance
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

 F02358EN-00.pdf | PDF (0.1Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0726.pdf | PDF (0.1Mo)