

Product sheet



MOSAIC™ LEGRAND

Mosaic™ - Flush mounting box Batibox - 3 modules /Vela - depth 40 mm -dry partitions

REF. 080049 | EAN. 3245060800499

[> Visit e-catalogue](#)

Product characteristics

- Multi-gang boxes - For wiring equipment using screws - Drilling diameter 67 mm - Supplied with 1 removable divider for accomodating extended functions For 83.5 mm fixing centres - Compatible with : Arteor and Mosaic ranges - Depth 40 - 3 modules horizontal mounting

Documentation

TECHNICAL DOCUMENTATION

- F00447EN-01.pdf | PDF (1.42Mo)
- F00447FR-01.pdf | PDF (1.34Mo)

CAD & Design specs / BIM

- BIM-LEGRAND-MOSAIC-2024-FRANCAIS.rvt | RVT (128.2Mo)
- BIM-LEGRAND-MOSAIC-2023-ENGLISH.rvt | RVT (126.68Mo)
- BIM-BTICINO-LIVING-NOW-2024-ENGLISH.rvt | RVT (151.63Mo)
- BIM-BTICINO-LIVING-NOW-2024-ANGLAIS.rvt | RVT (151.39Mo)
- BIM-LEGRAND-MOSAIC-2023-FRANCAIS.rvt | RVT (128.48Mo)
- Bticino_appareillage_Living_Now_2023_FR.rvt | RVT (66.08Mo)
- BIM-LEGRAND-MOSAIC-2024-ANGLAIS.rvt | RVT (125.56Mo)
- BIM-BTICINO-LIVING-NOW-2024-FRANCAIS.rvt | RVT (69.79Mo)

CATALOGUE PAGE & OTHERS

- ex223001_0811.pdf | PDF (0.2Mo)
- ex223001_0810.pdf | PDF (0.17Mo)

Agreements & Certificates

- NF-NF012_4462/A1 | (0.62Mo)
- OC / CB-FR_705863/M1 | (0.57Mo)