

Product sheet



HYPRA LEGRAND

Surface mounting socket Hypra - IP 44 - 380/415 V~ - 63 A - 3P+N+E - plastic

REF. 053724 | EAN. 3245060537241



[> Visit e-catalogue](#)

Product characteristics

- Hypra IP 44 sockets and plugs metal, plastic, rubber, IP 44/55 Prinsinter - LV 16 to 63 A and ELV 16 and 32 A - Conform to IEC 60309 - 1 and IEC 60309 - 2 - IP 44 according to IEC 60529 - IK 09 : plastic and rubber - IK 10 : metal according to IEC 62262 - Self - extinguishing : - 850°C (support of active parts) / 960 °C for Prinsinter) - 650 °C : plastic housing conform to IEC 60695 - 2 - 10 - 50°C to + 100°C (- 20°C for Prinsinter) LV surface mounting sockets 380 to 415 V~ 50/60 Hz - 63 A 3P+N+E - Plastic - 63 A

Documentation

TECHNICAL DOCUMENTATION

- [LE09817AA.pdf](#) | PDF (0.36Mo)
-  [F00138FR-04.pdf](#) | PDF (1.44Mo)
-  [F00138EN-04.pdf](#) | PDF (1.25Mo)

Agreements & Certificates

-  [OC / CB-FR_710636](#) | (0.64Mo)