

# Product sheet



## LEGRAND

MCCB - DRX 125 - thermal magnetic - Icu 20 kA - 415 V~ - 3P - In 63 A

REF. 027220 | EAN. 3414970344045

> [Visit e-catalogue](#)

## Product characteristics

- DRX 125 - thermal magnetic MCCBs from 15 to 125 A - For switching, control, isolation and protection of low - voltage electrical lines - Can be fitted with auxiliaries - Supplied with : - M5 terminal for In ≤ 50 A and M8 range for In 50 A - Fixing screws - Insulating shields (2 for 3P and 3 for 4P) - Fixed thermal and magnetic - Conform to IEC 60947 - 2, in compliance with NEMA
- DRX 125 Breaking capacity Icu 20 kA (415 V~) - 3P - 63 A

## Documentation

### TECHNICAL DOCUMENTATION

→ [Y1036G.pdf](#) | PDF (0.58Mo)

### CAD & Design specs / BIM

 [027068.dwg](#) | DWG (0.19Mo)

### CATALOGUE PAGE & OTHERS


 [ex223001\\_0132.pdf](#) | PDF (0.13Mo)

 [ex223001\\_0136.pdf](#) | PDF (0.07Mo)

 [ex223001\\_0138.pdf](#) | PDF (0.05Mo)

### Agreements & Certificates

 [LGRP-01099-V01.01-EN.pdf](#) | PDF (0.62Mo)

 [OC / CB-SE-101774A1](#) | (0.42Mo)