

Product sheet



LEGRAND

MCCB DRX \parallel 630 - thermal magnetic - 4P - Icu 36 kA
(415 V~) - In 500 A

REF. 027240 | EAN. 3414970344984

> [Visit e-catalogue](#)

Documentation

TECHNICAL DOCUMENTATION

- [LE07105AA.pdf](#) | PDF (2.2Mo)
- [F01945EN00_DRX630.pdf](#) | PDF (1.01Mo)

CAD & Design specs / BIM

- [027249.dwg](#) | DWG (0.24Mo)

CATALOGUE PAGE & OTHERS

- [ex223001_0144.pdf](#) | PDF (0.03Mo)
- [ex223001_0142.pdf](#) | PDF (0.06Mo)
- [ex223001_0134.pdf](#) | PDF (0.08Mo)

Agreements & Certificates

- [OC / CB-SE-91829](#) | (1.1Mo)
- [LGRP-00534-V01.01-EN.pdf](#) | PDF (0.98Mo)