

# Product sheet



## P 17 TEMPRA LEGRAND

Surface mounting socket P17 - IP66/67 - 200/250 V~ - 16 A - 3P+E

REF. 555355 | EAN. 3245065553550

[> Visit e-catalogue](#)

## Product characteristics

- P 17 Tempra Pro IP 66/67 LV 16 and 32 A Surface mounting sockets - Two possible angles (5° or 25°) 200/250 V~ - 16 A - 3P+E

## Documentation

### TECHNICAL DOCUMENTATION

 F01811FR-02.pdf | PDF (3.67Mo)

 LE05815AA-01.pdf | PDF (2.53Mo)

 F01811EN-03.pdf | PDF (9.37Mo)


### CAD & Design specs / BIM


 surface\_no\_interlocked\_sockets\_200\_250V.rfa | RFA (1.31Mo)


 555355.dwg | DWG (0.13Mo)

 Prises\_non\_verrouillées\_saillies\_200\_250V.rfa | RFA (1.31Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0527.pdf | PDF (0.11Mo)

 ex223001\_0533.pdf | PDF (0.07Mo)


 ex223001\_0534.pdf | PDF (0.06Mo)

### Agreements & Certificates

 IMQ-CA02.05950 | (0.42Mo)

 CCC-CQC2016010203837679 | (3.47Mo)

 OC / CB-FR\_710665 | (0.7Mo)

 LGRP-2014-112-V1-EN.pdf | PDF (1.02Mo)