

# Product sheet



## P 17 TEMPRA LEGRAND

Surface mounting socket P17 - IP66/67 - 380/415 V~ - 32 A - 3P+N+E

REF. 555459 | EAN. 3245065554595

[> Visit e-catalogue](#)

## Product characteristics

- P 17 Tempra Pro IP 66/67 LV 16 and 32 A Surface mounting sockets - Two possible angles (5° or 25°) 380/415 V~ - 32 A - 3P+N+E

## Documentation

### TECHNICAL DOCUMENTATION

 F01811FR-02.pdf | PDF (3.67Mo)

 LE05815AA-01.pdf | PDF (2.53Mo)

 F01811EN-03.pdf | PDF (9.37Mo)

### CAD & Design specs / BIM

 Prises\_non\_verrouillées\_saillies\_380\_415V.rfa | RFA (1.47Mo)

 555459.dwg | DWG (0.13Mo)

 surface\_no\_interlocked\_sockets\_380\_415V.rfa | RFA (1.47Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0527.pdf | PDF (0.11Mo)


 ex223001\_0533.pdf | PDF (0.07Mo)

 ex223001\_0534.pdf | PDF (0.06Mo)

### Agreements & Certificates

 IMQ-CA02.05951 | (0.42Mo)

 OC / CB-FR\_710665 | (0.7Mo)

 LGRP-2014-112-V1-EN.pdf | PDF (1.02Mo)