

# Product sheet



P 17 TEMPRA LEGRAND

Surface mounting socket P17 Pro - IP 66/67 - 200/250 V~ - 63 A - 2P+E

REF. 555554 | EAN. 3414970734884

> [Visit e-catalogue](#)

## Product characteristics

- P 17 Tempra Pro IP 66/67 LV 63 and 125 A Surface mounting sockets 200/250 V~ - 63 A - 2P+E

## Documentation

### TECHNICAL DOCUMENTATION

 F02385FR-01.pdf | PDF (2.98Mo)

 LE05815AA-01.pdf | PDF (2.53Mo)

 F02385EN-01.pdf | PDF (1.98Mo)

### CAD & Design specs / BIM

 555554.dwg | DWG (0.17Mo)

surface\_no\_interlocked\_sockets\_200\_250V.rfa | RFA (1.31Mo)

Prises\_non\_verrouillées\_saillies\_200\_250V.rfa | RFA (1.31Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0535.pdf | PDF (0.06Mo)

 ex223001\_0528.pdf | PDF (0.13Mo)

 ex223001\_0534.pdf | PDF (0.06Mo)

### Agreements & Certificates

 OC / CB-FR\_706516 | (1.27Mo)

 CCC-CQC2018010203055862 | (2.31Mo)

 LGRP-00201-V01.01-EN.pdf | PDF (0.71Mo)