

Product sheet



LINKEO LEGRAND

Linkeo fan kit with 2 fans and thermostat

REF. 646430 | EAN. 3245066464305

[> Visit e-catalogue](#)

Product characteristics

- Integrated thermostat, adjustable from 10° to +80 °C
- Power 36W
- Current 0,25A
- Equipped with 3 x 0.75mm² flexible power supply cords, 2.5m long with standard 2P+E French/German plug 230V
- Plate made of steel with anthracite grey RAL 7016 finishing (same as cabinet)

The product's benefits

Installation

- Easy to install : once you have knocked out the cut-out with a mallet, the kit is fixed directly to the cabinet end plate, using self-tapping screws with pins (supplied).

Usage

- Ensures a high extraction output rate of 180 m³ per hour

Documentation

TECHNICAL DOCUMENTATION

- [LE09826AA-02.pdf](#) | PDF (1.38Mo)
- [F02420EN-01.pdf](#) | PDF (2.28Mo)
- [F02421FR-01.pdf](#) | PDF (2.29Mo)
- [LE09825AA-03.pdf](#) | PDF (1.09Mo)
- [F02420FR-01.pdf](#) | PDF (2.28Mo)

CATALOGUE PAGE & OTHERS

- [ex223001_0943.pdf](#) | PDF (0.07Mo)
- [ex223001_0944.pdf](#) | PDF (0.14Mo)