

# Product sheet



LEGRAND

On-line double conversion UPS - 3000 VA - 2400 W-  
backup time 10 min

REF. 310121 | EAN. 3245063101210





[> Visit e-catalogue](#)

## Product characteristics

- Keor S - On - line double conversion UPS (tower) - single phase - For industrial environment (food industry, laboratories ...) or applications requiring long backup time (electro - medical ...) - Installation : downstream power generators. Possibility to add batteries for extended autonomy. Parallel connection possible : up to 4 UPSs. Advanced management depending on the battery discharge level - Sinusoidal output - LCD screen - Self - diagnosis - Power factor : 0,9 - Integrated automatic bypass and maintenance bypass. Integrated slot for installing a communication interface for Ethernet network connection, to be ordered separately - Cold Start Function. Microprocessor control - Telephone line/Internet (RJ 11/ RJ45 ) - Remote emergency shutdown function ("Emergency Power Off" - EPO). Equipped with 4 wheels for easy moving of the UPS
- UPS - The stated backup time in minutes is estimated and may vary according to the load characteristics, operating conditions and environment - Nominal power : 3000 VA - Active power : 2400 W - Backup time : 10 min - Weight : 53 kg

## Documentation

### TECHNICAL DOCUMENTATION

-  [EXB22078\\_EN.pdf](#) | PDF (4.09Mo)
-  [UPS\\_LGR\\_0087\\_FR\\_AA.pdf](#) | PDF (0.22Mo)
-  [UPS\\_LGR\\_0087\\_GB\\_AA.pdf](#) | PDF (0.19Mo)
-  [EXB21082\\_EN.pdf](#) | PDF (11.02Mo)

### Agreements & Certificates

-  [LGRP-00667-V01.01-EN.pdf](#) | PDF (0.68Mo)

### CATALOGUE PAGE & OTHERS

-  [ex223001\\_0932.pdf](#) | PDF (0.09Mo)