

Product sheet



LEGRAND

On-line double conversion UPS - tower - 2000 VA - 1800 W

REF. 310156 | EAN. 3414970499295

[> Visit e-catalogue](#)

Product characteristics


- Keor LP - On - line double conversion UPS (tower) - single phase VFI - For security systems, lighting systems, CCTV, servers. Ideal for environments with frequent electrical disturbances - Installation : downstream power generators. Advanced management depending on the battery discharge level - Self - diagnosis. Power factor : 0,9 - Automatic internal bypass, manual bypass for external maintenance (optional) - Integrated slot for installing a communication interface for Ethernet network connection, to be ordered separately - Cold Start function - Microprocessor control - Telephone line/Internet protection (RJ 11/ RJ45) - Internal network interface Cat.No 3 108 82 for remote protection of equipment and systems - Remote emergency shutdown function ("Emergency Power Off" - EPO)
- UPS with IEC sockets - The stated backup time in minutes is estimated and may vary according to the load characteristics, operating conditions and environment - Nominal power : 2000 VA - Active power : 1800 W - Backup time : 5 min - No. of sockets IEC (10 A) : 6 - Weight : 17 kg

Documentation

TECHNICAL DOCUMENTATION

-  [UPS_LGR_0086_GB_AA.pdf](#) | PDF (0.24Mo)
-  [EXB22078_EN.pdf](#) | PDF (4.09Mo)
-  [EXB21082_EN.pdf](#) | PDF (11.02Mo)
-  [UPS_LGR_0086_FR_AA.pdf](#) | PDF (0.24Mo)
-  [LE07360AC.pdf](#) | PDF (25.66Mo)

Agreements & Certificates

-  [LGRP-2015-266-V1-EN.pdf](#) | PDF (0.64Mo)

CATALOGUE PAGE & OTHERS

-  [ex223001_0931.pdf](#) | PDF (0.13Mo)